


SECTION A-A
SCALE 1:1

Specifications

A. Material

Insulator: PA9T, UL94 V-0, Black
Contact: Copper Alloy, T=0.12mm
Mid Plate: Stainless Steel, T=0.15mm
Shell: Stainless Steel, T=0.30mm
EMI: Stainless Steel, T=0.10mm

B. Plating

Contact Area: 15u" Au over 80u" min. Nickel
Solder Tails: 2u" Au over 80u" min. Nickel
Shell: 60u" min. Nickel
EMI: 50u" min. Nickel
Mid Plate: 40u" min. Matte Tin over 30u" min. Nickel

C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins

Voltage Rating: 48V

Power Rating: 240W

Contact Resistance: 40mΩ max initial
50mΩ max after test

Dielectric Withstanding Voltage: 100V AC

Insulation Resistance: 100MΩ min.




D. Mechanical & Environmental

Operating Temperature: -25℃ to +85℃


Mating Force: 5 to 20 N.


Unmated Force: 6 to 20 N after test

Durability: 10,000 cycles




Laser Welding
Points(4x)



Part Number			Product Description			 <i>Connecting the Future</i> www.szywf.com.cn www.szywf.cn	
PTCFW-H22F-032			USB 3.2 Gen 2 Type C Receptacle, Horizontal, DualRow SMT, Mid Mount, 0.8mm Offset, 24 Pin				
DWG.No.	P-TCF-198		Tolerances Unspecified		Units: Metric(mm)		
Revision	A0		X.X ±0.35	X° ±5°			
Designed	Lee	11/30/20	X.XX ±0.25	X.X° ±2°			
Approved	Allen	11/30/20	X.XXX ±0.15				
						Sheet No. 1/3	




Sheet No. 1/3



RECOMMENDED PCB LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05


PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TX1+	B11	TX1+
A3	TX1-	B10	TX1-
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RX2-	B3	TX2-
A11	RX2+	B2	TX2+
A12	GND	B1	GND



Part Number			Product Description			
PTCFW-H22F-032			USB 3.2 Gen 2 Type C Receptacle, Horizontal, DualRow SMT, Mid Mount, 0.8mm Offset, 24 Pin			
DWG.No.	P-TCF-198		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X	± 0.35	X°	$\pm 5^\circ$
Designed	Lee	11/30/20	X.XX	± 0.25	X.X°	$\pm 2^\circ$
Approved	Allen	11/30/20	X.XXX	± 0.15		





	REEL	CARTON
QUANTITY (PCS)	900	9000

Part Number			Product Description		
PTCFW-H22F-032			USB 3.2 Gen 2 Type C Receptacle, Horizontal, DualRow SMT, Mid Mount, 0.8mm Offset, 24 Pin		
DWG.No.	P-TCF-198		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ±0.35	X° ±5°	
Designed	Lee	11/30/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	11/30/20	X.XXX ±0.15		

Connecting the Future

www.szywf.com.cn
www.szywf.cn

Sheet No. 3/3