



A	B	C
③	DIM E±0.2	



1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： $125\text{V}, \text{AC}$ 。
4. 接触电阻： $\leq 0.02\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$

High photosynthesis 台高(H)	The female seat neight 母座单高(H1)	The male seat neight 公座单高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9

WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1	Part No	CKT	A	B	C	D	E
	B0810FAA35-8P	8	2.40	3.50	5.10	4.20	4.00
	B0810FAA35-10P	10	3.20	4.30	5.90	5.00	
B0810FAA35-12P	12	4.00	5.10	6.70	5.80		
B0810FAA35-14P	14	4.80	5.90	7.50	6.60		
B0810FAA35-16P	16	5.60	6.70	8.30	7.40		
B0810FAA35-18P	18	6.40	7.50	9.10	8.20		
B0810FAA35-20P	20	7.20	8.30	9.90	9.00		
2	B0810FAA35-22P	22	8.00	9.10	10.70	9.80	8.00
	B0810FAA35-24P	24	8.80	9.90	11.50	10.60	
	B0810FAA35-26P	26	9.60	10.70	12.30	11.40	
B0810FAA35-28P	28	10.40	11.50	13.10	12.20		
B0810FAA35-30P	30	11.20	12.30	13.90	13.00		
B0810FAA35-32P	32	12.00	13.10	14.70	13.80		
B0810FAA35-34P	34	12.80	13.90	15.50	14.60		
3	B0810FAA35-36P	36	13.6	14.70	16.30	15.40	8.00
	B0810FAA35-38P	38	14.40	15.50	17.10	16.20	
	B0810FAA35-40P	40	15.20	16.30	17.90	17.00	
B0810FAA35-44P	44	16.80	17.90	19.50	18.60		
B0810FAA35-50P	50	19.20	20.30	21.90	21.00		
B0810FAA35-60P	60	23.20	24.30	25.90	25.00		
B0810FAA35-70P	70	27.20	28.30	29.90	29.00		
4	B0810FAA35-80P	80	31.20	32.30	33.90	33.00	8.00
	B0810FAA35-100P	100	39.20	40.30	41.90	41.00	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM. x.x x.xx x.xxx GENERAL ANGLE: ±1.0°		TOL. ±0.50 ±0.20 ±0.10 ±1.0°		TITLE: 0.8 Pitch 双槽 立式 BTB 母座(单高3.5)		APPROVED: WILL	
UNIT: mm		SCALE: none		SHEET: 2 of 2		DWG. SIZE: A4	
LAYER: bxconn		DRAWN: ELLA		CHECKED: MAX		DATE:	