






A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1	Part No	CKT	A	B	C	D	E
	B0810FAA45-8P	8	2.40	3.50	5.10	4.20	4.00
	B0810FAA45-10P	10	3.20	4.30	5.90	5.00	
	B0810FAA45-12P	12	4.00	5.10	6.70	5.80	
B0810FAA45-14P	14	4.80	5.90	7.50	6.60		
B0810FAA45-16P	16	5.60	6.70	8.30	7.40		
B0810FAA45-18P	18	6.40	7.50	9.10	8.20		
B0810FAA45-20P	20	7.20	8.30	9.90	9.00		
2	B0810FAA45-22P	22	8.00	9.10	10.70	9.80	8.00
	B0810FAA45-24P	24	8.80	9.90	11.50	10.60	
	B0810FAA45-26P	26	9.60	10.70	12.30	11.40	
	B0810FAA45-28P	28	10.40	11.50	13.10	12.20	
B0810FAA45-30P	30	11.20	12.30	13.90	13.00		
B0810FAA45-32P	32	12.00	13.10	14.70	13.80		
B0810FAA45-34P	34	12.80	13.90	15.50	14.60		
B0810FAA45-36P	36	13.6	14.70	16.30	15.40		
B0810FAA45-38P	38	14.40	15.50	17.10	16.20		
B0810FAA45-40P	40	15.20	16.30	17.90	17.00		
B0810FAA45-44P	44	16.80	17.90	19.50	18.60		
B0810FAA45-50P	50	19.20	20.30	21.90	21.00		
B0810FAA45-60P	60	23.20	24.30	25.90	25.00		
B0810FAA45-70P	70	27.20	28.30	29.90	29.00		
B0810FAA45-80P	80	31.20	32.30	33.90	33.00		
B0810FAA45-100P	100	39.20	40.30	41.90	41.00		



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM.		TOL.		TITLE: 0.8 Pitch 双槽 立式 BTB 母座(单高4.5)			
x.x		±0.50		DWG. NO.: B0810FAA45-XP			
x.xx		±0.20		CHECKED: MAX			
x.xxx		±0.10		PART NO.: B0810FAA45-XP			
GENERAL ANGLE:		±1.0°		DRAWN: ELLA			
UNIT:		mm		SCALE: none		APPROVED: WILL	
SHEET:		2 of 2		DWG. SIZE: A4		LAYER: bxconn	



WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A

