




A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.		NAME		DATE

Part No	CKT	A	B	C	D	E
B0810FAA30-8P	8	2.40	3.50	5.10	4.20	4.00
B0810FAA30-10P	10	3.20	4.30	5.90	5.00	
B0810FAA30-12P	12	4.00	5.10	6.70	5.80	
B0810FAA30-14P	14	4.80	5.90	7.50	6.60	
B0810FAA30-16P	16	5.60	6.70	8.30	7.40	
B0810FAA30-18P	18	6.40	7.50	9.10	8.20	
B0810FAA30-20P	20	7.20	8.30	9.90	9.00	
B0810FAA30-22P	22	8.00	9.10	10.70	9.80	
B0810FAA30-24P	24	8.80	9.90	11.50	10.60	8.00
B0810FAA30-26P	26	9.60	10.70	12.30	11.40	
B0810FAA30-28P	28	10.40	11.50	13.10	12.20	
B0810FAA30-30P	30	11.20	12.30	13.90	13.00	
B0810FAA30-32P	32	12.00	13.10	14.70	13.80	
B0810FAA30-34P	34	12.80	13.90	15.50	14.60	
B0810FAA30-36P	36	13.6	14.70	16.30	15.40	
B0810FAA30-38P	38	14.40	15.50	17.10	16.20	
B0810FAA30-40P	40	15.20	16.30	17.90	17.00	
B0810FAA30-44P	44	16.80	17.90	19.50	18.60	
B0810FAA30-50P	50	19.20	20.30	21.90	21.00	
B0810FAA30-60P	60	23.20	24.30	25.90	25.00	
B0810FAA30-70P	70	27.20	28.30	29.90	29.00	
B0810FAA30-80P	80	31.20	32.30	33.90	33.00	
B0810FAA30-100P	100	39.20	40.30	41.90	41.00	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: 0.8 Pitch 双槽 立式 BTB 母座(单高3.0)			
x.x	±0.50	DWG. NO.: B0810FAA30-XP		CHECKED: MAX	
x.xx	±0.20	PART NO.: B0810FAA30-XP		DRAWN: ELLA	
x.xxx	±0.10	UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4
GENERAL	ANGLE: ±1.0°	LAYER: bxconn		APPROVED: WILL	