



| A    |  | B           |  | C       |  | D    |  | E    |  |
|------|--|-------------|--|---------|--|------|--|------|--|
| REV. |  | DESCRIPTION |  | ECN NO. |  | NAME |  | DATE |  |
|      |  |             |  |         |  |      |  |      |  |

|                 |     |       |       |       |                |      |       |       |       |       |       |
|-----------------|-----|-------|-------|-------|----------------|------|-------|-------|-------|-------|-------|
| 1               | 2   | 3     | 4     | 5     | PIN NO         | PIN  | DIM A | DIM B | DIM C | DIM D | DIM E |
|                 |     |       |       |       | B0510FAA45-8P  | 8    | 1.50  | 2.55  | 4.70  | 3.40  | 4.00  |
|                 |     |       |       |       | B0510FAA45-10P | 10   | 2.00  | 3.05  | 5.20  | 3.90  |       |
|                 |     |       |       |       | B0510FAA45-12P | 12   | 2.50  | 3.55  | 5.70  | 4.40  |       |
|                 |     |       |       |       | B0510FAA45-14P | 14   | 3.00  | 4.05  | 6.20  | 4.90  |       |
|                 |     |       |       |       | B0510FAA45-16P | 16   | 3.50  | 4.55  | 6.70  | 5.40  |       |
|                 |     |       |       |       | B0510FAA45-18P | 18   | 4.00  | 5.05  | 7.20  | 5.90  |       |
|                 |     |       |       |       | B0510FAA45-20P | 20   | 4.50  | 5.55  | 7.70  | 6.40  |       |
|                 |     |       |       |       | B0510FAA45-22P | 22   | 5.00  | 6.05  | 8.20  | 6.90  |       |
|                 |     |       |       |       | B0510FAA45-24P | 24   | 5.50  | 6.55  | 8.70  | 7.40  |       |
| B0510FAA45-26P  | 26  | 6.00  | 7.05  | 9.20  | 7.90           | 8.00 |       |       |       |       |       |
| B0510FAA45-28P  | 28  | 6.50  | 7.55  | 9.70  | 8.40           |      |       |       |       |       |       |
| B0510FAA45-30P  | 30  | 7.00  | 8.05  | 10.20 | 8.90           |      |       |       |       |       |       |
| B0510FAA45-32P  | 32  | 7.50  | 8.55  | 10.70 | 9.40           |      |       |       |       |       |       |
| B0510FAA45-34P  | 34  | 8.00  | 9.05  | 11.20 | 9.90           |      |       |       |       |       |       |
| B0510FAA45-36P  | 36  | 8.50  | 9.55  | 11.70 | 10.40          |      |       |       |       |       |       |
| B0510FAA45-38P  | 38  | 9.00  | 10.05 | 12.20 | 10.90          |      |       |       |       |       |       |
| B0510FAA45-40P  | 40  | 9.50  | 10.55 | 12.70 | 11.40          |      |       |       |       |       |       |
| B0510FAA45-44P  | 44  | 10.50 | 11.05 | 13.70 | 12.40          |      |       |       |       |       |       |
| B0510FAA45-50P  | 50  | 12.00 | 13.05 | 15.20 | 13.90          |      |       |       |       |       |       |
| B0510FAA45-60P  | 60  | 14.50 | 15.55 | 17.70 | 16.40          |      |       |       |       |       |       |
| B0510FAA45-70P  | 70  | 17.00 | 18.05 | 20.20 | 18.90          |      |       |       |       |       |       |
| B0510FAA45-80P  | 80  | 19.50 | 20.55 | 22.70 | 21.40          |      |       |       |       |       |       |
| B0510FAA45-100P | 100 | 24.50 | 25.55 | 27.70 | 26.40          |      |       |       |       |       |       |

|                                                         |  |                                               |  |                |  |               |  |
|---------------------------------------------------------|--|-----------------------------------------------|--|----------------|--|---------------|--|
| GENERAL TOLERANCE                                       |  | DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD |  |                |  | BXCONN®       |  |
| DIM.<br>x.x<br>x.xx<br>x.xxx<br>GENERAL ANGLE:<br>±1.0° |  | TITLE: 0.5 Pitch 双槽 立式 BTB 母(单高4.5)           |  |                |  | QR CODE       |  |
|                                                         |  | DWG. NO.: B0510FAA45-XP                       |  | CHECKED: MAX   |  | DRAWN: ELLA   |  |
|                                                         |  | PART NO.: B0510FAA45-XP                       |  | APPROVED: WILL |  |               |  |
| UNIT: mm                                                |  | SCALE: none                                   |  | SHEET: 2 of 2  |  | DWG. SIZE: A4 |  |
|                                                         |  |                                               |  | LAYER: bxconn  |  |               |  |