






0.10



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$

Part No	CKT	A	B	C	D
BX-BTB0.5-53HMD1-4PCZ	2*2	0.50	2.54	3.50	2.20
BX-BTB0.5-53HMD1-6PCZ	2*3	1.00	3.04	4.00	2.70
BX-BTB0.5-53HMD1-8PCZ	2*4	1.50	3.54	4.50	3.20
BX-BTB0.5-53HMD1-10PCZ	2*5	2.00	4.04	5.00	3.70
BX-BTB0.5-53HMD1-12PCZ	2*6	2.50	4.54	5.50	4.20
BX-BTB0.5-53HMD1-14PCZ	2*7	3.00	5.04	6.00	4.70
BX-BTB0.5-53HMD1-16PCZ	2*8	3.50	5.54	6.50	5.20
BX-BTB0.5-53HMD1-18PCZ	2*9	4.00	6.04	7.00	5.70
BX-BTB0.5-53HMD1-20PCZ	2*10	4.50	6.54	7.50	6.20
BX-BTB0.5-53HMD1-22PCZ	2*11	5.00	7.04	8.00	6.70
BX-BTB0.5-53HMD1-24PCZ	2*12	5.50	7.54	8.50	7.20
BX-BTB0.5-53HMD1-26PCZ	2*13	6.00	8.04	9.00	7.70
BX-BTB0.5-53HMD1-28PCZ	2*14	6.50	8.54	9.50	8.20
BX-BTB0.5-53HMD1-30PCZ	2*15	7.00	9.04	10.00	8.70
BX-BTB0.5-53HMD1-32PCZ	2*16	7.50	9.54	10.50	9.20
BX-BTB0.5-53HMD1-34PCZ	2*17	8.00	10.04	11.00	9.70
BX-BTB0.5-53HMD1-36PCZ	2*18	8.50	10.54	11.50	10.20
BX-BTB0.5-53HMD1-38PCZ	2*19	9.00	11.04	12.00	10.70
BX-BTB0.5-53HMD1-40PCZ	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
BX-BTB0.5-53HMD1-80PCZ	2*40	19.50	21.54	22.50	21.20

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-BTB0.5-53HMD1-XPCZ		版本 REV.	A	
						X.: ±0.50	±1°		审核 CHECK	EVA	品名 TITLE	0.5 Pitch D型单槽侧插BTB母座(单高5.3)	页次 SHEET	1/1			
															X.X: ±0.20	客户料号 CUTM.NO.	
②	0.5 Pitch D型单槽侧插 BTB母座端子	铜合金/表面点镀金						单位 UNITS	MM		 Bossie (博锡)						
1		2		3		4		5		6		7		8		9	