








P.C.B LAYOUT (Copper-side view)



Rating: 3A 24V DC
Contact Resistance: 100 mΩ Max.
Operating temperature: -25℃ ~ 80℃
Operating force: 3-20N
Operating Life: 5,000 cycles



Model No.	DC-005-20A	DC-005-25A
PIN	ø2.0	ø2.5

③	PIN	—	1	Brass	Sn Plating	—
②	Terminal	—	3	Phosphor bronze/Brass	Sn Plating	—
①	Housing	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE								
DRAWN		LIUCAN		2021.11.9							
CHECKED					TITLE:		全铜大电流款				
APPROVALS					PART NO.		DC-005				
TOLERANCES ARE		30~以上		±0.30	ANGLE	UNIT: mm		SCALE: 1:1		PROJ: 	
		10~30		±0.20							
		5~10		±0.15							
		~ 5		±0.10							
				±2'	DRAWING NO.				SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			