






ROHS



电路原理图



REV.	ECN NO.	DESCRIPTION	DRAW	DATE


NOTES:

1.ELECTRICAL CHARACTERS:

- 1-1.RATING: DC 30V 0.5A;
- 1-2.CONTATCT RESISTANCE: $\leq 30\text{m}\Omega$;
- 1-3.INSULATION RESISTANCE: $\geq 100\text{M}\Omega$ DC 500V;
- 1-4.WITHSTANDING VOLTAGE:AC 500V(50Hz)/1min;
- 1-5.LIFE:5,000 CYCLES;

2.MECHANICAL CHARACTERISTICS:

- 2-1.INSERTION&EXTRACTION FORCE:3~30N;
- 2-2.OPERATING TEMPERATURE: $-30^{\circ}\text{C}\sim+70^{\circ}\text{C}$;



6	插针	1	H59(Y)黄铜棒 $\phi=2.5\text{mm}$	D. Cu/Sn
5	平片	1	H62(Y)黄铜带 $\delta=0.4\text{mm}$	D. Cu/Sn
4	后盖	1	PA工程塑料	黑
3	弯片	1	H62(Y)黄铜带 $\delta=0.35\text{mm}$	D. Cu/Sn
2	簧片	1	QSn6.5-0.1(Y)锡青铜带 $\delta=0.3\text{mm}$	D. Sn/Sb
1	底座	1	PA	黑
序号	名称	数量	材料	备注

COSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK					
APPROVAL					
TOLERANCES ARE					
30-150	± 0.35	ANGLE			
10-30	± 0.2				
5-10	± 0.15				
0-5	± 0.1				
		$\pm 3^{\circ}$			
TITLE		DC电源连接器D6. 4C2. 5(SMT)		REV.	A
PART NO.		LAIL-DC30-D6. 4C2. 5G-T		UNITS	mm
DWG.NO.				Projection	