







		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



台高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： 125V, AC 。
4. 接触电阻： $\leq 0.02\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$ 。



序号	品名	材质	B0511FBA22-36P	2X18	8.50	9.70	11.20	12.56	10.60
①	0.5 Pitch B型 单槽立式BTB母座底座	LCP UL94 V-0 颜色:米黄色	B0511FBA22-38P	2X19	9.00	10.20	11.70	13.06	11.10
			B0511FBA22-40P	2X20	9.50	10.70	12.20	13.56	11.60
			B0511FBA22-44P	2X22	10.50	11.7	13.20	14.56	12.60
②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面镀锡/表面点镀金	B0511FBA22-50P	2X25	12.00	13.2	14.70	16.06	14.10
			B0511FBA22-60P	2X30	14.50	15.7	17.20	18.56	16.60
③	0.5 Pitch B型 单槽立式BTB母座薄片	铜合金/表面镀锡	B0511FBA22-70P	2X35	17.00	18.2	19.70	21.06	19.10
			B0511FBA22-80P	2X40	19.50	20.7	22.20	23.56	21.60

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x.x ±0.50 x.xx ±0.20 x.xxx ±0.10 GENERAL ANGLE: ±1.0°		TITLE: 0.5 Pitch B型 单槽 立式 BTB 母座(单高2.2)						
		DWG. NO.: B0511FBA22-XP			CHECKED: MAX			
		PART NO.: B0511FBA22-XP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 2	DWG. SIZE: A4	LAYER: bxcnn	APPROVED: WILL	

