



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2026.07.30



SPECIFICATIONS



Current rating: 0.2A, AC, DC
Voltage rating: 30V AC,DC
Temperature range: -25°C ~ +85°C
Insulation resistance: 100MΩ Min.
Withstanding voltage: 200V AC/ minute
Contact resistance: 30mΩ Max.

Material:



Insulator: LCP UL 94V-0 Black
Contact: Brass
Finish: Plated Gold
Circuits: 2-16P
Mate with:XFCN M0611RS series Housing
Ordering Code:

M0611HI-XX-GB


Pin位数 2-16P



MATED CONDITION



No.of PIN/ROW	Dimension			
	A	B	C	D
2	1.36	1.80	0.60	1.65
3	1.96	2.40	1.20	2.25
4	2.56	3.00	1.80	2.85
5	3.16	3.60	2.40	3.45
6	3.76	4.20	3.00	4.05
7	4.36	4.80	3.60	4.65
8	4.96	5.40	4.20	5.25
10	6.16	6.60	5.40	6.45
12	7.36	7.80	6.60	7.65
14	8.56	9.00	7.80	8.85
16	9.76	10.20	9.00	10.05



X.±0.50	X.°±	PART NO: M0611HI-XX-GB		XFCN 兴飞连接器			
.X±0.25	.X°±						
.XX±0.15	.XX°±	TITLE: 0.60mm IDC Style Connectors		0769-82001899			
.XXX±0.10	.XXX°±			www.xfconn.com			
UNITS:	mm			DWG NO:			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang	VIEW			
		CHKD	Liu Wei				
		DRAW	Chen HongJiang	SCALE	SHEET	REV	
		DATE	2026.07.30	NONE	1/1	A1	