

序号	品名	材质
①	0.5 Pitch双槽立式 BTB母座嵌芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式 BTB母座双盖	LCP UL94 V-0颜色:黑色

High photosynthesis 合高 (H)	The female seat neight 母座半高 (H1)	The male seat neight 公座半高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x.xx ±0.50 x.xx ±0.20 x.xxx ±0.10 GENERAL ANGLE: ±1.0°		TITLE: 0.5 Pitch 双槽 立式 BTB 母(单高4.0)						
		DWG. NO.: B0510FAA40-XP			CHECKED: MAX			
		PART NO.: B0510FAA40-XP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1	PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
	B0510FAA40-8P	8	1.50	2.55	4.70	3.40	4.00
	B0510FAA40-10P	10	2.00	3.05	5.20	3.90	
	B0510FAA40-12P	12	2.50	3.55	5.70	4.40	
	B0510FAA40-14P	14	3.00	4.05	6.20	4.90	
	B0510FAA40-16P	16	3.50	4.55	6.70	5.40	
	B0510FAA40-18P	18	4.00	5.05	7.20	5.90	
	B0510FAA40-20P	20	4.50	5.55	7.70	6.40	
	B0510FAA40-22P	22	5.00	6.05	8.20	6.90	
	B0510FAA40-24P	24	5.50	6.55	8.70	7.40	
B0510FAA40-26P	26	6.00	7.05	9.20	7.90		
2	B0510FAA40-28P	28	6.50	7.55	9.70	8.40	8.00
	B0510FAA40-30P	30	7.00	8.05	10.20	8.90	
	B0510FAA40-32P	32	7.50	8.55	10.70	9.40	
	B0510FAA40-34P	34	8.00	9.05	11.20	9.90	
	B0510FAA40-36P	36	8.50	9.55	11.70	10.40	
	B0510FAA40-38P	38	9.00	10.05	12.20	10.90	
	B0510FAA40-40P	40	9.50	10.55	12.70	11.40	
	B0510FAA40-44P	44	10.50	11.05	13.70	12.40	
	B0510FAA40-50P	50	12.00	13.05	15.20	13.90	
	B0510FAA40-60P	60	14.50	15.55	17.70	16.40	
3	B0510FAA40-70P	70	17.00	18.05	20.20	18.90	
	B0510FAA40-80P	80	19.50	20.55	22.70	21.40	
	B0510FAA40-100P	100	24.50	25.55	27.70	26.40	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM. x.x x.xx x.xxx GENERAL ANGLE: ±1.0°		TITLE: 0.5 Pitch 双槽 立式 BTB 母(单高4.0)				QR CODE	
		DWG. NO.: B0510FAA40-XP		CHECKED: MAX			
		PART NO.: B0510FAA40-XP		DRAWN: ELLA			
UNIT: mm		SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	