








Specifications

A. Material

Insulator: PA9T, UL94 V-0, Black
Contact: Copper Alloy, T=0.12mm
Mid Plate: Stainless Steel, T=0.15mm
Shell: Stainless Steel, T=0.30mm
EMI: Stainless Steel, T=0.10mm

B. Plating

Contact Area: 3u" Au over 60u' min. Nickel
Solder Tails: Gold Flash Au over 60u" min. Nickel
Shell: 50u" min. Nickel
EMI: 50u" min. Nickel
Mid Plate: No Plating

C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins
Voltage Rating: 48V
Power Rating: 240W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental


Operating Temperature: -25℃ to +85℃
Mating Force: 5 to 20 N.
Unmated Force: 6 to 20 N after test
Durability: 10,000 cycles

Part Number			Product Description			
PTCFW-H12E-029			USB 2.0 Type C Receptacle, Vertical, SMT, H=7.46mm, 24 Pin			
DWG.No.	P-TCF-180		Tolerances Unspecified		Units:	
Revision	A0		X.X ±0.35	X° ±5°	Metric(mm)	
Designed	Lee	12/10/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	12/10/20	X.XXX ±0.15			





www.szywf.com.cn
www.szywf.cn

Sheet No. 1/3




RECOMMENDED PCB LAYOUT (COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05



WITH PICK UP COVER
SCALE 1:1


PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TX1+	B11	TX1+
A3	TX1-	B10	TX1-
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RX2-	B3	TX2-
A11	RX2+	B2	TX2+
A12	GND	B1	GND






Part Number			Product Description			
PTCFW-H12E-029			USB 2.0 Type C Receptacle, Vertical, SMT, H=7.46mm, 24 Pin			
DWG.No.	P-TCF-180		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X	± 0.35	X°	$\pm 5^\circ$
Designed	Lee	12/10/20	X.XX	± 0.25	X.X°	$\pm 2^\circ$
Approved	Allen	12/10/20	X.XXX	± 0.15		






SEE DETAIL X



	REEL	CARTON
QUANTITY (PCS)	600	6000

Part Number			Product Description		
PTCFW-H12E-029			USB 2.0 Type C Receptacle, Vertical, SMT, H=7.46mm, 24 Pin		
DWG.No.	P-TCF-180		Tolerances Unspecified		
Revision	A0		X.X	±0.35	X° ±5°
Designed	Lee	12/10/20	X.XX	±0.25	X.X° ±2°
Approved	Allen	12/10/20	X.XXX	±0.15	

Units:
Metric(mm)



www.szywf.com.cn
www.szywf.cn

Sheet No. 3/3