






ROHS



TECHNICAL FEATURES

- 1.OPERATING TEMPERATURE: -25 TO 70°C
- 2.RATED ELECTRONEGATIVITY: DC 30V 1.0A
- 3.CONTACT RESISTANCE: $\leq 30\text{ m}\Omega$
- 4.INSULATION RESISTANCE: $\geq 100\text{M}\Omega$
- 5.WITHSTAND VOLTAGE: AC500V (50HZ) /Min
- 6.INSERTION AND EXTRACTION FORCE: 3-25N
- 7.LIFESPAN: 5,000 TIMES



6	REAR COVER	1PCS	PBT/PPA/PA46	BLACK
5	BASE SEAT	1PCS	PBT/PPA/PA46	BLACK
4	INSERT A NEEDLE	1PCS	IRON SHEET	Ni PLATING
3	BULLET PIECE	1PCS	MANGANESE STEEL	Sn PLATING
2	CURVED SHEET	1PCS	IRON SHEET	Sn PLATING
1	FLAT PLATE	1PCS	IRON SHEET	Sn PLATING
NO	NAME	Q'TY	MATERIALS	REMARKS

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	DC电源连接器D6. 3C2. 0弯插	REV.	A		
30-150	±0.35	PART NO.	LAIL-DC30-D6. 3C2. 0G-W	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							