







Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	3.80	2.50	6.50	6.30
Alternate				



Ordering Information

PZ 200		- *	- N	- S	- *	- **	- *	- P
No. of Rows 1=Single Row 2=Dual Row		No. of Pins 2-40Pin	Type P=直針 R=彎針 S=斜針	Length (Plastic) (高度)	Contact G0:Gold G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Plating Flash Gold Gold Gold Gold Gold Gold Gold	R=Reel +Cap (編管-退包圈)	Post (帶柱)

			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审 核 CHECK					
			X.X ± 0.30	批 准 APPROVAL	产品名称 TITLE	2.00双排 排针 贴片 编带+盖 (塑高2.0)	版 本 REV.	A	
1	初版发行		X.XX ± 0.20		产品料号 PART NO.	PZ200-2-N-S-2.0-XX-R	单 位 UNITS	mm	
			X.XXX ± 0.10	比 例 SCALE					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ± 3.0°	投 影 Projection	 材料 MATERIAL		页 次 SHEET	1/1	



深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	2.00双排 排针 贴片 编带+盖 (塑高2.0)	版 本 REV.	A
产品料号 PART NO.	PZ200-2-N-S-2.0-XX-R	单 位 UNITS	mm
材 料 MATERIAL		页 次 SHEET	1/