




规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
30 milliohms MAX
- 4.耐电压:Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion
1.0kgf(MIN)

原材料:Material:

- 1.塑胶:Housing:
Hing Temperature Thermaplastics,
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: Copper Alloy C2680/SPCC

Nickel Plating

成品图 MANUFACTURE DWG		东莞市文章济美电子有限公司							
公差一览表 TOLERANCE UNLESS OTHERWISE		日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING		DWG NO.	5001-USB10800201-081-B
.X±0.15	X.±5°	日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING		DWG NO.	5001-USB10800201-081-B
.XX±0.10	.X±2°	审核 CHECKED		比例 SCALE	1:1	设计 DESIGN	LIUFU	品名 NAME	规格6.3直插金脚
.XXX±0.05	.XX±1°	核准 APPROVE		角法 VIEW	⊕			版本 VER	AO 页教 SHEET 001