

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		220606

Material

Insulator:Nylon 9T(UL94V-0)

TERMINAL:phosphor Bronze

TERMINAL Plated:Gold over Nickel
or Tin

Specification

Current rating:7A




instant CURRENT:10A

Contact Resistance:30MΩ

Insulation Resistance:100MΩ


Dielectric Voltage:500V

Operdting Temperature:-40°~105°



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm



No. of Pins	Dimension	
	DIM. B	DIM. A
03	4.00	8.60
04	6.00	10.60
05	8.00	12.60
06	10.00	14.60
07	12.00	16.60
08	14.00	18.60
09	16.00	20.60
10	18.00	22.60
11	20.00	24.60
12	22.00	26.60

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司					
▽ M ▽ C		MM		INCH	MATERIAL:		HRC:								
	. X	±0.25	. X	⑩----	DRAWN BY				DATE		TITLE: Battery 2.0PH 180度DIP 4.2H 公座				
	. XX	±0.15	. XX	⑩----	CHECKED BY				DATE						
	. XXX	±0.05	. XXX	⑩----											
	ANGULAR ±1°				⊕ ⊞ THIRD ANGLE PROJECTION				REVISE ON CAD ONLY						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														
				APPROVED BY				DATE		PART NO.		DWG NO.		SHEET NO. 1/1	
JME20M**-H4225-B										A4					