




Notes:

1. Material:

1.1 Housing: thermoplastic high temp. UL94V-0;

1.2 Terminal: copper alloy.

1.3 Fitting Nail: copper alloy.

2. FINISH:

2.1 Terminal:

50u"Min Nickel under plating over all

1:1u"Gold on contact and solder area.

M:5u"Gold on contact and 1u"Gold on solder area.

R:10u" Min Gold on contact and 1u"Gold on solder area.

S:15u"Gold on contact and 1u"Gold on solder area.

E:30u"Gold on contact and 1u"Gold on solder area.

2.2 Fitting Nail:

50u"Min Nickel under plating over all

80~150u" Matte-Tin over all.

3. Product must comply HF RoHS specification.

4. Product No:

ANC05-S 67 R * * - **

CKTS

CONNECTOR TYPE

R:SMT H=3.00

REMARKS

HF:Halogen free

Housing Black

PLATING

I:Gold flash

M:5u" Min

R:10u" Min

S:15u" Min

E:30u" Min

PACKING

A:Tape&Reel

C:Tube

CUSTOMER DRAWING				东莞市文章济美电子有限公司			
Tolerance Unspecified (未注公差)		Size(图幅):		Product Name(产品名称):			
0.0 ±0.25 0° ±5°		Unit(单位):		0.5Pitch H=3.00 M.2 CARD CONNECTOR M KEY 3.0H TYPE			
0.00 ±0.15 0°0 ±3°		Scale(比例):		Product No(产品料号):			
0.000 ±0.10 0°00 ±1°		1:1		5001-C05-S67RIA-AC0			
Project View (投影视角)		Page(页数):		Designer(设计)			
1 OF 3		Rev(版本):		Checked(审核)			
A		A		Approved(核准)			
Rev		Date		张孝雄			
版本		日期		制/修订人			
Original Issue		2024/01/25		张孝雄			
Change Description		变更内容					

