





SPECIFICATIONS

Current Rating: 1.5 Amps  
Insulation Resistance:1000M $\Omega$ , Min  
Contact Resistance: 20m $\Omega$ , Max  
Withstanding Voltage: AC 500V  
Operation Temperature:-40° to+105°  
Contact Material: Brass  
Standard: PA6T  
Insrlator Material: Polyester(UL 94V-0)  
Contact Plating: Gold Flash  
Max.Processing Temp: 240° C for30-60seconds  
(260° C for5seconds)



RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE: ±0.05 (TOP VIEW)

|   | 1      |        | 2      |        | 3      |        | 4      |        | 5      |        | 6      |        | 7      |        | 8      |        | 9      |        |
|---|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
|   | 10. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
| B | 4      | 2.00   | 6.6    | 24     | 22.00  | 26.60  | 42     | 40.00  | 44.60  | 60     | 58.00  | 62.60  |        |        |        |        |        |        |
|   | 8      | 6.00   | 10.60  | 26     | 24.00  | 28.60  | 44     | 42.00  | 46.60  | 62     | 60.00  | 64.60  |        |        |        |        |        |        |
|   | 10     | 8.00   | 12.60  | 28     | 26.00  | 30.60  | 46     | 44.00  | 48.60  | 64     | 62.00  | 66.60  |        |        |        |        |        |        |
|   | 12     | 10.00  | 14.60  | 30     | 28.00  | 32.60  | 48     | 46.00  | 50.60  | 66     | 64.00  | 68.60  |        |        |        |        |        |        |
|   | 14     | 12.00  | 16.60  | 32     | 30.00  | 34.60  | 50     | 48.00  | 52.60  | 68     | 66.00  | 70.6   |        |        |        |        |        |        |
|   | 16     | 14.00  | 18.60  | 34     | 32.00  | 36.60  | 52     | 50.00  | 54.60  | 70     | 68.00  | 72.60  |        |        |        |        |        |        |
|   | 18     | 16.00  | 20.60  | 36     | 34.00  | 38.60  | 54     | 52.00  | 56.60  |        |        |        |        |        |        |        |        |        |
|   | 20     | 18.00  | 22.60  | 38     | 36.00  | 40.60  | 56     | 54.00  | 58.60  |        |        |        |        |        |        |        |        |        |
|   | 22     | 20.00  | 24.60  | 40     | 38.00  | 42.60  | 58     | 56.00  | 60.60  |        |        |        |        |        |        |        |        |        |
|   |        |        |        |        |        |        |        |        |        |        |        |        |        |        |        |        |        |        |



深圳市韩下电子有限公司

UNLESS OTHIEWIXE SPECIFIED TOLERANCE

X : ±0.3 X° : ±5°  
X. X : ±0.2 X. X° : ±1°  
X. XX: ±0.1 X. XX° : ±0.5°

DRAWM NAME: HX JN2.0-2x2P TP H6.4

| SIZE | A4 | SCALE | N:1 | PROUCT NO. |
|------|----|-------|-----|------------|
| REV  | A  | UNIT  | mm  | PROJECT    |

DRAW: 黄彬 2022/04/21 CHECKED: 张伟 2022/04/21 APPROVED: 罗小春 2022/04/21