

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
	原始图档		JACK		250608

Material

Insulator:Nylon 9T(UL94V-0)

Contact:phosphor Bronze

Contact Plated:Gold over Nickel or Tin

Specification

Current rating:5A




instant CURRENT:7A

Contact Resistance:30mΩ


Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°



No:of pins	Dimension		
	DIM.A	DIM.B	DIM.C
02	7.00	5.10	2.00
03	9.00	7.10	4.00
04	11.00	9.10	6.00
05	13.00	11.10	8.00
06	15.00	13.10	10.00
07	17.00	15.10	12.00
08	19.00	17.10	14.00
09	21.00	19.10	16.00
10	23.00	21.10	18.00
11	25.00	23.10	20.00
12	27.00	25.10	22.00



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司		
	. X	MM ±0.25	. X	INCH @----	MATERIAL:	HRC:			
	. XX	±0.15	. XX	@----	DRAWN BY	DATE	TITLE: 新款2.0PH 180度DIP 无柱 母座		
	. XXX	±0.05	. XXX	@----	CHECKED BY	DATE			
	ANGULAR ±1°				APPROVED BY	DATE	THIRD ANGLE PROJECTION		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								
	JME20F**-WZ25-B						PART NO.	DWG NO.	SHEET NO. 1/1
							A4		