








项 目 Mapx	设 变 内 容 Modification	日 期 Date	修 改 人 Draw	核 准 Approve



- 备注:
1. 材质:
1.1 端子: C5191R-EH, T=0.15mm.
1.2 胶芯: LCP+30%GF, 颜色: 黑色
1.3 外壳: SUS 304R-1/2H, T0.30mm
2. 电镀:
2.1 端子: 电镀镍底50u"Min. (焊接区域) 锡脚电镀亮锡80u"Min.
2.2 外壳: 电镀镍底50u"Min.
2.3

料号对照表:

品名	品名电镀规格
014101010-037	单排SMT LCP黑色镀金3u"
014109020-046	单排SMT PA46橙色镀金3u"
014106020-047	单排SMT PA46绿色镀金3u"
014102020-085	单排SMT LCP黑色镀金30u"
014102020-062	单排SMT LCP本色镀金3u"

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

成 品 图 MANUFACTURE DWG	
公 差 一 览 表 TOLERANCE UNLESS OTHERWISE	
.X±0.20	X.±5°
.XX±0.10	.X.±2°
.XXX±0.05	.XX±1°

东莞市文章济美电子有限公司

日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING		DWG NO.	5001-USB2101588-081-B
审核 CHECKED		比例 SCALE	1 : 1	设计 DESIGN	LIUFU	品 名 NAME	USB C F TYPE单排前金贴 后插 有柱外壳无凸包无弹CONN.
核准 APPROVE		角 法 VIEW	⊕ ⊖			版 本 VER	AO 页 数 SHEET 004