







技术参数 SPECIFICATIONS
间距(PITCH):0.5
极数(POLES):4~60
额定电压(VOLTAGE RATING):50V DC/AC
额定电流(CURRENT RATING):0.3A DC/AC
耐压值(WITHSTAND VOLTAGE):500V
工作温度(WORKING TEMPERATURE):-25℃~+85℃
绝缘电阻(INSULATION RESISTANCE):≥500MΩ
接触电阻(CONTACT RESISTANCE):≤30MΩ
双面接触(DOUBLE-SIDED CONTACT)


材料 MATERIAL
接触件(CONTACT):磷铜C5191T=0.15MM 镀NI 30~80U",
接触点镀金FU",焊脚镀金FU"
焊片(SOLDER TAB):黄铜C2801 T=0.15MM 镀锡,
NI 30~80U",锡SN 80~200U"
塑胶主体(HOUSING):LCP NC 耐热树脂(UL94V-0)
HEATRESISTANCE PLASTIC(UL94V-0)
锁条(BACK COVER):LCP BK耐热树脂(UL94V-0)
HEATRESISTANCE PLASTIC(UL94V-0)



PART. NO	PIN	A	B	C
F-FPCOM05P-G330	5P	2.00	3.00	6.00
F-FPCOM06P-G330	6P	2.50	3.50	6.50
F-FPCOM07P-G330	7P	3.00	4.00	7.00
F-FPCOM08P-G330	8P	3.50	4.50	7.50
F-FPCOM10P-G330	10P	4.50	5.50	8.50
F-FPCOM12P-G330	12P	5.50	6.50	9.50
F-FPCOM14P-G330	14P	6.50	7.50	10.50
F-FPCOM16P-G330	16P	7.50	8.50	11.50
F-FPCOM18P-G330	18P	8.50	9.50	12.50
F-FPCOM20P-G330	20P	9.50	10.50	13.50
F-FPCOM21P-G330	21P	10.00	11.00	14.00
F-FPCOM22P-G330	22P	10.50	11.50	14.50
F-FPCOM24P-G330	24P	11.50	12.50	15.50
F-FPCOM26P-G330	26P	12.50	13.50	16.50
F-FPCOM28P-G330	28P	13.50	14.50	17.50
F-FPCOM30P-G330	30P	14.50	15.50	18.50
F-FPCOM32P-G330	32P	15.50	16.50	19.50
F-FPCOM35P-G330	35P	17.00	18.00	21.00
F-FPCOM36P-G330	36P	17.50	18.50	21.50
F-FPCOM40P-G330	40P	19.50	20.50	23.50
F-FPCOM45P-G330	45P	22.00	23.00	26.00
F-FPCOM50P-G330	50P	24.50	25.50	28.50
F-FPCOM54P-G330	54P	26.50	27.50	30.50
F-FPCOM60P-G330	60P	29.50	30.50	33.50



RECOMMENDED P.C.B PATTERN LAYOUT
PCB布局



扁平线电缆

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: FPC0.5-XP 前插后锁 双触 H=2.0mm			
DRAWN: LYF	DATE: 2024-06-28	PART. NO.	F-FPCOMXXP-G330		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-FPC-00114	REV.	A LX00