

电气特性:Electrical:

PIN NU_BER	SIGNAL NAME
1	USB 电压
2	D-(负极)
3	D+(正极)
4	地线
5	SSRX-
6	SSRX+
7	GND(地线)
8	SSTX-
9	SSTX+
shell	SHIELD

1.5A/contact terminal

30V DC

30 milliohms MAX

500 V AC AT Sea Level

1000MEGA ohms MIN

	1.插拔力: Cnconnector Mate and Unmate Force Mate force:3.57kgf(MAX) Unmate force:1.02kgf(MIN)
--	--

Mate force:3.57kgf(MAX)

原材料:Material:

Hing Temperature Tnermaplastics,

3.外壳:Shell: Copper Alloy C2680/SPCC

端子四周镀60U”(MIN)—100U锡,“镀金1U”

外壳四周鍍60U”(MIN)镍

东莞市文章济美电子有限公司									
日期	2023.06.8	单位	MM	制图		DWG NO.	5001-USB1529574-081-B		
审核		比例	1 : 1	设计	LIUFU	品名			
批准		角法				版本	AO	页 数	001
APPROVE		VFW				VFR		SHEET	

