




PANEL CUT-OUT

Rating :
10A 250V AC T105 UL cUL
10A 250V AC VDE 3C KC
Fuse : 250VAC 6.3A 2.5W
Insert And Extract Force: 1.36kgf~6.8kgf
Operating Life: ≥5000 cycles
Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:3750V
AC (50-60Hz)1min
Leakage Current : 1mA
Insulation Resistance: ≥100MΩ 500V DC
Body Materil: NYLON 66 94V-2~0

			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			UP TO 5	±0.20	批 准 APPROVAL	产品名称 TITLE	Ac Inlet C14型	版本 REV.	A
1	初版发行		ABOVE 5 TO 30	±0.30	比 例 SCALE	产品料号 PART NO.	DB-14-F4-1.5	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±5°	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1