


WASHER



NUT

SPECIFICATIONS:





IMPEDANCE: 50 ohms

FREQUENCY RANGE: 0~6GHz

VSWR:1.5 MAX

WORKING VOLTAGE:500 V rms @ sea level

INSULATION RESISTANCE: 5000 MΩ




BOTTOM

TOP

Rev	描述 Description	变更编号 Change number	日期 Date
A	First issue	---	2023/05/30

5	NUT	BRASS	NICKEL	1PCS
4	WSAHER	BRASS	NICKEL	1PCS
3	INSULATOR	PTFE	WHITE	1PCS
2	CONTACT PIN	BRASS	GOLD	1PCS
1	BADY	BRASS	NICKEL	1PCS
No.	描述 Description	材质 Material	材质 Finish	数量 Qty/Unit

		The View		 DOSIN INDUSTRIAL(HK)CO.,LTD		Web:http://www.dosinconn.com	
单位 mm		页码 1/1		江门市德索连接器有限公司		Dosin2005@dosin-china.com	
unit		page		Jiangmen Dosin Connector Co., LTD		Tel:(0086)769-81153906	
图号				料号		产品名称	
Drawing NO				Part Number		Product name	
文件保密 File security This drawing shall not be copied, circulated or used for other purposes without permission. 本图纸未经允许, 不可复制、外传或它用				DS806FPS0284		R/P-SMA JACK FOR	
						PCB	
		未注公差 Unmarked tolerance		绘图		Wang YiWang	
		零部件 Parts		线性 Line		审核	
		X. ±0.5		≤10 ±1		Check	
		X.X ±0.20		10~50 ±1.5		客户确认	
		X.XX ±0.10		>50 ±4%		Customer confirmation	
		角度 angle ±3°					