










PENEL CUT-OUT



PCB LAYOUT

Rating:
7A 125V AC UL cUL
2.5A 250V AC VDE 3C KC
Insert And Extract Force: 1.36kgf~6.8kgf
Terminal Strength: $\geq 60N$
Operating Life: ≥ 6000 cycles
Withstand Voltage:
Between all terminals: 2500VAC (50~60Hz) 1min
Terminals to Base: 3750V AC (50~60Hz) 1min
Leakage Current: 1mA
Insulation Resistance: $\geq 100M\Omega$ 500V DC
Body Material: PC 94V-2~0

序号	名称	材料	处理	数量	备注
1	DB-8-5塑料件	PC	黑色	1	
2	DB-8-P9 端子	黄铜	镀锡	2	
3	DB-8-1DX 短插销	黄铜	镀镍	2	

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	DB-8 (电源插座)	版本 REV.	A
			X.X ± 0.30	批准 APPROVAL	产品料号 PART NO.	DB-8-5P9	单位 UNITS	mm
			X.XX ± 0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
1	初版发行		X.XXX ± 0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle $\pm 3.0^\circ$					