


Operation: 卧式/SMT 阻燃 3.6⊙大电流 DC 电源连接器 (Type-A)



LTEM NO.: DC-045B-T13 (Series)

(L9.0×W6.0×H4.8 DC-CONNECTORS)



邀您使用(微信)小程序

碩方电子开关&连接器选型手册

手机扫码即可进入...

Technical parameter

LEVEL		A[better product]	B[average product]
PROJECT			
Electrical Properties	Contact Rating	0.5A, 30V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
Durable Performance	There No Load	6,000 Cycles	5,000 Cycles
	Rated Load	5,000 Cycles	4,000 Cycles
Storage temp.		-35℃~+75℃(Operating Temp:)	
Operating Force		IF:35N MAX. (EF:10.0N MIN.)	
Heat Rrsistance		IR Reflow:235℃,5sec. Manual:350℃,3sec.	

表面貼裝 SMT


側向操作

精密部品 NICETY



可靠 STABILIZE

適合環保 RoHS

CIRCUIT DIAGRAM



Unit:mm



P.C.B LAYOUT

