




PANEL CUT-OUT

X	L
0.8	24
1.0	24.6
1.2	25.2
1.6~2.0	26.2

Rating:

15A 125V AC UL cUL

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength: $\geq 60N$

Operating Life: ≥ 6000 cycles

Withstand Voltage:

Between all terminals: 2500VAC (50-60Hz) 1min

Terminals to Base: 3750V AC (50-60Hz) 1min

Leakage Current: 1mA

Insulation Resistance: $\geq 100M\Omega$ 500V DC

Body Material: NYLON66 94V-2~0

序号	名称	材料	处理	数量	备注
1	DB-F-M(H)-W109基座	环阻PA66	白色	1	
2	DB-F-ML 弹片	黄铜	镀锡	1	
3	DB-F-MS(H) 弹片	黄铜	镀锡	2	

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核				
					CHECK	产品名称		版本	A
			X.X		批准	TITLE		REV.	
			X.XX		APPROVAL	产品料号		单位	mm
			X.XXX		比例	PART NO.		UNITS	
			Angle		SCALE			材料	
序号	变更内容	日期	投影		投影	MATERIAL		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE			Projection			SHEET	