





Product No: DS806FCS0243				
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	DENG	2022/10/27	Mr.chen



SPECIFICATIONS:

IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHz
VSWR: 1.5MAX
WORKING VOLTAGE: 500V /MAX
INSULATION RESISTANCE: 5000 MΩ
INTER CONTACT: ≤50ohms
OUTER CONTACT: ≤20ohms
WORKING TEMPERATURE RANGE: ≤ -40℃ +135℃

NOTE:

DRAWN:	DATE:	Tolerance	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR DIMENSIONS ARE: 0.5-8MM ±0.05MM 8-30MM ±0.20MM 30-120MM ±0.50MM	dosh.com DOSIN INDUSTRIAL(HK)CO.,LTD 东莞市德索五金电子有限公司 Dongguan Dosin Hardware Electronics Co.,Ltd.	Web: http://www.dosin.com dosin2005@dosin-china.com Tel: (0086)769-81153906 Fax: (0086)769-81875836
--------	-------	-----------	---	---	--

CHECKED: DENG

VIEW



Name: SMA JACK PLATE 2 HOTE

APPROVALS:

UNIT

MM

Product NO. DS806FPS0243

REV A

SCALE

1 : 1

Customer NO. /

SHEET: 1 OF 1