







PRODUCT NO:		DS806FPR-0110		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	W.cheng	2020/12/29	John kine
B				




RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHz
VSWR:1.5MAX
WORKING VOLTAGE:500V RMS@SEA LEVEL
INSULATION RESISTANCE: 5000 ohms min
TEMPERATURE RANGE: -65°C TO +165°C
RELATIVE TEMPERATURE:≤95%(40°C±2°C)



NUT



WASHER

1	BODY	BRASS	GOLD	1	NOTE:	TOLERANCE	UNLESS OTHERWISE SPECIFIED TOLERANCES: DRINCHES ARE 0.5-8MM±0.20MM 8-30MM±0.40MM 30-120MM±0.50MM	 	NAME:	SMA ANGLE JACK			
2	INSULATOR	TEFLON	WHITE	1									
3	CONTACT PIN	BRASS	GOLD	1									
4	NUT	BRASS	GOLD	1									
5	WASHER	BRASS	GOLD	1	DRAWN				Dongguan Dosin Hardware Electronics Co.,Ltd. Fax: (0086) 769-81875836				
6					W.cheng	2020/12/29							
7					CHECKED								
8						UNIT	MM		SIZE A	PRODUCT NO: DS806FPR-0110	REV A		
9									DATE TIME	CAD FILE			
10					APPROVALS	SCALE	1 : 1		2020/12/29	H/companydrawings/BD	SHEET: 1 OF 1		
A		B		C		D		E		F		G	
COMPONENT NUMBER		MATERIAL		FINISH		QTY							