






PRODUCT NO: DS806FPR-0136


REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	CHEN	2021/7/13	John kine
B				




RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHz
VSWR: 1.5MAX
WORKING VOLTAGE: 500V RMS@SEA LEVEL
INSULATION RESISTANCE: 5000 ohms min
TEMPERATURE RANGE: -65°C TO +165°C
RELATIVE TEMPERATURE: ≤95%(40°C±2°C)



NUT



WASHER

1	BODY	BRASS	GOLD	1
2	INSULATOR	TEFLON	WHITE	1
3	CONTACT PIN	BRASS	GOLD	1
4	NUT	BRASS	GOLD	1
5	WASHER	BRASS	GOLD	1
6				
7				
8				
9				
10				
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY

NOTE:

DRAWN
W.cheng

2020/12/29


CHECKED

APPROVALS

TOLERANCE

UNLESS OTHERWISE SPECIFIED
TOLERANCES IN INCHES ARE
0.5-8MM±0.05MM
8-30MM±0.20MM
30-120MM±0.50MM

VIEW



UNIT

MM

SCALE

1 : 1



DOSIN INDUSTRIAL(HK)CO.,LTD

东莞市德索五金电子有限公司

Dongguan Dosin Hardware Electronics Co.,Ltd. Fax:(0086)769-81875836

Web: http://www.dosinconn.com

dosin2005@dosin-china.com

E-mail: dosin2005@163.com

Tel: (0086)769-81153906

NAME: RP SMA JACK ANGLE PCB CONNECTOR

SIZE A PRODUCT NO: DS806FPR-0136

REV A

DATE TIME
2021/7/13CAD FILE
H/companydrawings/BD

SHEET: 1 OF 1