





SECTION A-A

RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

NOTES:

1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK

2.TERMINAL/GROUND PLANE:PHOSPHOR BRONZE
PLATING:10u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.

3.CODING INFORMATION: BTB332-xxxS-B3R-01

- WATER CODE
- PACKING: R: CARRIER REEL
- MATERIAL: 3:LCP
- COLOR: B:BLACK
- S:SOCKET / PIN
- PLATING: G:GOLD FLASH 2:3u'' GOLD IN CONTACT AREA, MATTE IIN ON TATL
  3:5u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  4:10u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  5:15u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  6:30u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
- 0.8 BTB HIGHLY: 32--3.25H
- BTB CONNECTOR SERIES

CKT	A.	B.
40	21.28	20.13
80	41.28	40.13
120	61.28	60.13
160	81.28	80.13
200	101.28	100.13

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD
CHECKED:	DATE:	TITLE: BTB0.8-40P 双排母座 塑高3.25 立贴带柱（合高5.2）
DRAWN: YKX	DATE: 2026-7-07	PART.NO. Z-BTB0840P-F003
		UNIT mm SCALE free
		FILE NO. Ckmtw-BTB-C003 REV. A LXWO