






TOLERANCE:	比例: 1:1	品名(Title):	TYPE C 24P四脚插立贴5.6	
X. ±0.25	单位: mm		(脚长0.95)	
X.X ±0.15	视角: 	料号(P/N):	Type-C-24P-LTH5.5-B	
X.XX ±0.10				
X.XXX ±0.05				
X.* ±1°	版本: A/0	设计(Design):	zxc	审核(Checked):

3.1 工作温度: $-30^{\circ}\text{C} \sim +85^{\circ}\text{C}$

装吸取盖示意图

Technical drawing illustrating the dimensions for the suction cover assembly:

- Top view dimensions: 4.50 ± 0.15 (width) and 8.50 ± 0.15 (length).
- Side view dimensions: 1.08 ± 0.15 (height of the main body) and 7.0 ± 0.15 (total height including the base).



PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSTXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND