










RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$




SECTION A-A



TYPE C USB技术要求:

1. 电气性能
 - 1.1 额定电流 3A
 - 1.2 额定电压: 5V.
 - 1.2 耐电压: 500 V(AC) for 1 min.
 - 1.3 接触阻抗: 40m Ω Max.
可靠性和环境测试后阻抗变化不得超过10m Ω .
 - 1.4 绝缘阻抗: 100 M Ω Min.
2. 机械性能
 - 2.1 插入力: 5~20N. 拔出力: 6~20N.
 - 2.2 寿命测试 10000 Max.
 - 2.3 推力: 50N min.
 - 2.4 剥离强度: 150N min.
 - 2.5 扭曲强度: 0.75Nm
3. 材料要求
 - 4.1 胶芯材料: LCP
 - 4.2 外壳材料: SUS201
 - 4.3 端子材料: C2680
4. 盐雾要求: 24H
5. 工作温度: -20° C~85° C



-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表		东莞市文章济美电子有限公司				
				TITLE: Type C 母座 14PIN 產品名稱: 立插 H=10.5		
X.X :±0.30	X.X° :±5°	APPD: 核准:	DWG NO: 產品料號: Type-C-14P-ZCH10.3-B			
X.XX :±0.20	X.XX° :±2°	CHECK: 校對:	DATE	SCALE	UNIT	PAGE
X.XXX:±0.10	X.XXX° :±1°	DRAW: 繪圖: LIUPENG	20210308	1:1	mm	1/1