




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\ \Omega$.
5. 绝缘电阻: $\geq 100\text{M}\ \Omega$

序号	品名	材质
①	0.5 Pitch C型单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型单槽立式BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C
BTB0.5-GH1.3-10PCLT2	2X5	2.00	3.40	5.50
BTB0.5-GH1.3-12PCLT2	2X6	2.50	3.90	6.00
BTB0.5-GH1.3-14PCLT2	2X7	3.00	4.40	6.50
BTB0.5-GH1.3-16PCLT2	2X8	3.50	4.90	7.00
BTB0.5-GH1.3-18PCLT2	2X9	4.00	5.40	7.50
BTB0.5-GH1.3-20PCLT2	2X10	4.50	5.90	8.00
BTB0.5-GH1.3-22PCLT2	2X11	5.00	6.40	8.50
BTB0.5-GH1.3-24PCLT2	2X12	5.50	6.90	9.00
BTB0.5-GH1.3-26PCLT2	2X13	6.00	7.40	9.50
BTB0.5-GH1.3-28PCLT2	2X14	6.50	7.90	10.00
BTB0.5-GH1.3-30PCLT2	2X15	7.00	8.40	10.50
BTB0.5-GH1.3-32PCLT2	2X16	7.50	8.90	11.00
BTB0.5-GH1.3-34PCLT2	2X17	8.00	9.40	11.50
BTB0.5-GH1.3-36PCLT2	2X18	8.50	9.90	12.00
BTB0.5-GH1.3-38PCLT2	2X19	9.00	10.40	12.50
BTB0.5-GH1.3-40PCLT2	2X20	9.50	10.90	13.00
.....	...	...	...	...
BTB0.5-GH1.3-100PCLT2	2X50	24.50	25.90	28.00

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE: 0.5 Pitch C型单槽立式 BTB公座业务图(单高1.3)	
.X±0.20		BTB0.5-GH1.3-NPCLT2		
.XX±0.10		DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SHEET 1/1

合高(H)	公座单高	母座单高
1.5	1.3	1.4
2.0	1.3	1.9
2.5	1.3	2.4