








SECTION A-A

公座与母座装配后


NOTES:

1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK

2.TERMINAL/GROUND PLANE:PHOSPHOR BRONZE
PLATING:10u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.


3.CODING INFORMATION: BTB3xx-xxxP-B3R-01

- WATER CODE
- PACKING: R: CARRIER REEL
- MATERIAL: 3:LCP
- COLOR: B:BLACK
- P:PLUG
- PIN
- PLATING: G:GOLD FLASH 2:3u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  3: 5u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  4:10u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  5:15u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
  6:30u'' GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
- 0.8 BTB
  HIGHLY:42--4.26H, A2-10.26H.
- BTB CONNECTOR SERIES



H	H1
4.267	4.064
7.267	7.064
10.267	10.063

CKT	A.	B.
40	20.00	18.48
80	40.00	38.48
120	60.00	58.48
160	80.00	78.48
200	100.00	98.48



RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD
CHECKED:	DATE:	TITLE: BTB0.8-40P 双排公座 塑高4.26 立贴 带柱 （合高5.2）
DRAWN: YKX	DATE: 2026-7-07	PART.NO. Z-BTB0840P-M003
		UNIT mm SCALE free
		FILE NO. Ckmtw-BTB-C004 REV. A LXW0