



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

东莞市文章济美电子有限公司

.X: ±0.35		.X*: ±5.0"		INTENDED USE:		TITLE: TYPE-C 16PIN 加高	
.XX: ±0.25		.XX*: ±3.0"		CUSTOMER DRAWING (客户图)		H=5.90 成品	
.XXX:±0.20		.XXX*:±1.5"		APPD.:		PART NO.: SEE TABLE	
MAT'L:				DWG. NO.:		Type-C-16P-JGSKH5.9-B	
SEE NOTES				SCALE: 1:1		PAGE: 1/1	
FINISH:		DR.: Len.Song		UNIT: MM		REV.: A0	