








High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围:-40° C~85° C.
 3. 额定电压:50V, AC.
 4. 接触电阻:≤0.02 Ω.
 5. 绝缘电阻:≥100M Ω

适用线路板

序号	品名	材质
1	0.5 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0 颜色:黑色
2	0.5 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金
3	0.5 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0 颜色:黑色.

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTB0.5-GH1.3-8PALT1	8	1.50	2.50	4.70	3.40	4.00
BTB0.5-GH1.3-10PALT1	10	2.00	3.00	5.20	3.90	
BTB0.5-GH1.3-12PALT1	12	2.50	3.50	5.70	4.40	
BTB0.5-GH1.3-14PALT1	14	3.00	4.00	6.20	4.90	
BTB0.5-GH1.3-16PALT1	16	3.50	4.50	6.70	5.40	
BTB0.5-GH1.3-18PALT1	18	4.00	5.00	7.20	5.90	
BTB0.5-GH1.3-20PALT1	20	4.50	5.50	7.70	6.40	
BTB0.5-GH1.3-22PALT1	22	5.00	6.00	8.20	6.90	
BTB0.5-GH1.3-24PALT1	24	5.50	6.50	8.70	7.40	
BTB0.5-GH1.3-26PALT1	26	6.00	7.00	9.20	7.90	
BTB0.5-GH1.3-28PALT1	28	6.50	7.50	9.70	8.40	8.00
BTB0.5-GH1.3-30PALT1	30	7.00	8.00	10.20	8.90	
BTB0.5-GH1.3-32PALT1	32	7.50	8.50	10.70	9.40	
BTB0.5-GH1.3-34PALT1	34	8.00	9.00	11.20	9.90	
BTB0.5-GH1.3-36PALT1	36	8.50	9.50	11.70	10.40	
BTB0.5-GH1.3-38PALT1	38	9.00	10.00	12.20	10.90	
BTB0.5-GH1.3-40PALT1	40	9.50	10.50	12.70	11.40	
BTB0.5-GH1.3-44PALT1	44	10.50	11.50	13.70	12.40	
BTB0.5-GH1.3-50PALT1	50	12.00	13.00	15.20	13.90	
BTB0.5-GH1.3-60PALT1	60	14.50	15.50	17.70	16.40	
BTB0.5-GH1.3-70PALT1	70	17.00	18.00	20.20	18.90	
BTB0.5-GH1.3-80PALT1	80	19.50	20.50	22.70	21.40	
BTB0.5-GH1.3-100PALT1	100	24.50	25.50	27.70	26.40	

GENERAL TOLERANCES
UNLESS SPECIFIED

X.±0.50	±1°
.X±0.20	
.XX±0.10	

MANUFACTURE DWG

深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
BTB0.5-GH1.3-NPALT1

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:
0.5 Pitch双槽立式BTB公(单高1.3)

CUSTOMER	SIZE A4	UNITS MM
	SCALE N:A	SHEET 1/1