





技术指标:

- 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
- 3. 额定电压: 50V, AC.
- 4. 接触电阻: $\leq 0.02\ \Omega$.
- 5. 绝缘电阻: $\geq 1000\text{M}\ \Omega$

序号	品名	材质
①	0.8 Pitch F型 单槽立式BTB公座胶芯	PA9T UL94 V-0, 颜色:黑色
②	0.8 Pitch F型 单槽立式公座端子	铜合金/表面点镀金
总高(H)		公座单高(H1)
4.00		2.80
4.50		3.30
5.00		3.80
5.50		4.30
6.00		4.80
6.50		5.30
7.00		5.80
		母座单高(H2)
		2.90
		3.40
		3.90

Part No	CKT	A	B	C	D
BTB0.8-GH3.3-6PFLT1	2*3	4.30	2.80	1.60	3.40
BTB0.8-GH3.3-8PFLT1	2*4	5.10	3.60	2.40	4.20
BTB0.8-GH3.3-10PFLT1	2*5	5.90	4.40	3.20	5.00
BTB0.8-GH3.3-12PFLT1	2*6	6.70	5.20	4.00	5.80
BTB0.8-GH3.3-14PFLT1	2*7	7.50	6.00	4.80	6.60
BTB0.8-GH3.3-16PFLT1	2*8	8.30	6.80	5.60	7.40
BTB0.8-GH3.3-18PFLT1	2*9	9.10	7.60	6.40	8.20
BTB0.8-GH3.3-20PFLT1	2*10	9.90	8.40	7.20	9.00
BTB0.8-GH3.3-30PFLT1	2*15	13.90	12.40	11.20	13.00
BTB0.8-GH3.3-40PFLT1	2*20	17.90	16.40	15.20	17.00
BTB0.8-GH3.3-50PFLT1	2*25	21.90	20.40	19.20	21.00
BTB0.8-GH3.3-60PFLT1	2*30	25.90	24.40	23.20	25.00
BTB0.8-GH3.3-70PFLT1	2*35	29.90	28.40	27.20	29.00
BTB0.8-GH3.3-80PFLT1	2*40	33.90	32.40	31.20	33.00
BTB0.8-GH3.3-90PFLT1	2*45	37.90	36.40	35.20	37.00
BTB0.8-GH3.3-100PFLT1	2*50	41.90	40.40	39.20	41.00

GENERAL TOLERANCES UNLESS SPECIFIED		 HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE: 0.8 Pitch F型单槽立式		
.X±0.20		BTB0.8—GH3.3—NPFLT1	BTB公座业务图(单高3.3)		
.XX±0.10		DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1