






Part No	CKT	A	B	C
BTB0.8-MH11.7-20PBLT1	2*10	7.20	13.80	12.20
BTB0.8-MH11.7-22PBLT1	2*11	8.00	14.60	13.00
BTB0.8-MH11.7-24PBLT1	2*12	8.80	15.40	13.80
BTB0.8-MH11.7-26PBLT1	2*13	9.60	16.20	14.60
BTB0.8-MH11.7-28PBLT1	2*14	10.40	17.00	15.40
BTB0.8-MH11.7-30PBLT1	2*15	11.20	17.80	16.20
BTB0.8-MH11.7-32PBLT1	2*16	12.00	18.60	17.00
BTB0.8-MH11.7-34PBLT1	2*17	12.80	19.40	17.80
BTB0.8-MH11.7-36PBLT1	2*18	13.60	20.20	18.60
BTB0.8-MH11.7-38PBLT1	2*19	14.40	21.00	19.40
BTB0.8-MH11.7-40PBLT1	2*20	15.20	21.80	20.20
BTB0.8-MH11.7-42PBLT1	2*21	16.00	22.60	21.00
BTB0.8-MH11.7-44PBLT1	2*22	16.80	23.40	21.80
BTB0.8-MH11.7-46PBLT1	2*23	17.60	24.20	22.60
BTB0.8-MH11.7-48PBLT1	2*24	18.40	25.00	23.40
BTB0.8-MH11.7-50PBLT1	2*25	19.20	25.80	24.20
.....	...	...	...	...
BTB0.8-MH11.7-200PBLT1	2*100	79.20	85.80	84.20



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40° C~85° C.
3. 额定电压: 100V, AC.
4. 接触电阻: ≤0.05 Ω.
5. 绝缘电阻: ≥500M Ω

序号	品名	材质	GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd				
①	0.8 Pitch B型立式 BTB母座胶芯	LCP UL94 V-0, 颜色:本色	X.±0.50	±1°	PART NO.	TITLE: 0.8 Pitch B型立式 BTB母座业务图(单高11.7)			
②	0.8 Pitch B型立式 BTB母座端子	铜合金/表面点镀金	.X±0.20		BTB0.8-MH11.7-NPBLT1	DESIGN: James	CUSTOMER	SIZE	UNITS
			.XX±0.10					A4	MM
③	0.8 Pitch B型立式 BTB母座吸盖	不锈钢	MANUFACTURE DWG		CHED: Talen		SCALE	SHEET	
					APPD: Sophia		N:A	1/2	



7.7

9.00

10.00

11.00

12.00

11.7

13.00

14.00

15.00

16.00


15.7

17.00

18.00

19.00

20.00

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE: 0.8 Pitch B型立式	
.X±0.20		BTB0.8-MH11.7-NPBLT1	BTB母座业务图(单高11.7)	
.XX±0.10		DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SCALE N:A
				SHEET 2/2