






RoHS Compliant

REV.	MODIFICATION	ECN No.	NAME	DATE
A0	NEW		LEN.SONG	2022.01.05



备注:
1. 材质:
1.1 胶芯: LCP+30%G.F UL94V-0
1.2 端子: H65铜, T=0.15mm; 半金镍1μ"
1.3 外壳: SUS201, T=0.30mm; 镀镍80μ" MIN.
2. 主要特性:
2.1 额定电流: 3.0A.
2.2 接触阻抗: 40MILLTOHMS MAX.
2.3 绝缘阻抗: 150V DC/100 MEGA OHMS MIN.
2.4 耐压测试: 100V AC/ 1MA MAX.
2.5 沾锡性: 温度250±5℃, 时间5±0.5s.
2.6 插入力: 5~20N 2. 拔出力: 8~20N.
使用寿命: 3000次、拔出力 5N MIN.
2.7 盐雾测试: 通过24H盐水盐雾无生锈现象.
2.8 工作温度: -30℃~+80℃.



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

东莞市文章济美电子有限公司					
.X: ±0.35		.X*: ±5.0°		INTENDED USE:	
.XX: ±0.25		.XX*: ±3.0°		CUSTOMER DRAWING (客户图)	
.XXX: ±0.20		.XXX*: ±1.5°		APPD.:	
MAT'L.: SEE NOTES				CHKD.:	
FINISH:				DR.: Len.Song	
TITLE: TYPE-C 16P 沉板1.0 L=6.5 无弹片				PART NO.: SEE TABLE	
DWG. NO.: Type-C-16P-CB1.0-B				SCALE: 1:1	
UNIT: mm				PAGE: 1/1	
REV.: A0					