





序号	品名	材质
①	0.8 Pitch E型 单槽侧插BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch E型 单槽侧插BTB公座端子	铜合金/表面镀金

Part No	CKT	A	B	C	D
BTB0.8-GH3.5-4PECC1	2*2	0.80	2.35	3.35	2.60
BTB0.8-GH3.5-6PECC1	2*3	1.60	3.15	4.15	3.40
BTB0.8-GH3.5-8PECC1	2*4	2.40	3.95	4.95	4.20
BTB0.8-GH3.5-10PECC1	2*5	3.20	4.75	5.75	5.00
BTB0.8-GH3.5-12PECC1	2*6	4.00	5.55	6.55	5.80
BTB0.8-GH3.5-14PECC1	2*7	4.80	6.35	7.35	6.60
BTB0.8-GH3.5-16PECC1	2*8	5.60	7.15	8.15	7.40
BTB0.8-GH3.5-18PECC1	2*9	6.40	7.95	8.95	8.20
BTB0.8-GH3.5-20PECC1	2*10	7.20	8.75	9.75	9.00
BTB0.8-GH3.5-22PECC1	2*11	8.00	9.55	10.55	9.80
BTB0.8-GH3.5-24PECC1	2*12	8.80	10.35	11.35	10.60
BTB0.8-GH3.5-26PECC1	2*13	9.60	11.15	12.15	11.40
BTB0.8-GH3.5-28PECC1	2*14	10.40	11.95	12.95	12.20
BTB0.8-GH3.5-30PECC1	2*15	11.20	12.75	13.75	13.00
BTB0.8-GH3.5-32PECC1	2*16	12.00	13.55	14.55	13.80
BTB0.8-GH3.5-34PECC1	2*17	12.80	14.35	15.35	14.60
BTB0.8-GH3.5-36PECC1	2*18	13.60	15.15	16.15	15.40
BTB0.8-GH3.5-38PECC1	2*19	14.40	15.95	16.95	16.20
BTB0.8-GH3.5-40PECC1	2*20	15.20	16.75	17.75	17.00
.....	...	...	...	...	...
BTB0.8-GH3.5-80PECC1	2*40	31.20	32.75	33.75	33.00

- 技术指标:
- 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 - 2. 温度范围: $-40^{\circ}C \sim 85^{\circ}C$.
 - 3. 额定电压: 125V, AC.
 - 4. 接触电阻: $\leq 0.02 \Omega$.
 - 5. 绝缘电阻: $\geq 100M \Omega$

GENERAL TOLERANCES UNLESS SPECIFIED		 HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE: 0.8 Pitch E型单槽侧插		
.X±0.20		BTB0.8—GH3.5—NPECC1	BTB公座业务图(单高3.5)		
.XX±0.10		DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1