







RoHS 2.0

PIN NUMBER	SIGNAL NAME
PIN 1	Vbus
PIN 2	D-
PIN 3	D+
PIN 4	GND
PIN 5	StdA_SSRX-
PIN 6	StdA_SSRX+
PIN 7	GND_DRAIN
PIN 8	StdA_SSTX-
PIN 9	StdA_SSTX+
SHELL	GND



3D VIEW



REV.	ECN	NO.	DESCRIPTION	DATE	DESIGN
A1.	/.		重新核对图面	21.01.04	LiHui
			HD	22.06.27	LZR

NOTES:

1. MATERIAL:

- 1.1. HOUSING: LCP ,COLOR IS BLUE;
- 1.2. CONTACT: BRASS (H65 T=0.20mm);
- 1.3. SHELL: COLD ROLLED IRON (SPCC,T=0.3mm);

2. FINISH:

- 2.1. TERMINAL:
CONTACT AREA: GOLD PLATED G/Fu";
SOLDER AREA: PLATED OVER TIN;
- 2.2. SHELL: NI PLATED OVER ALL ;

3. ELECTRICAL:

- 3.1. VOLTAGE RATING: 30 VAC RMS;
- 3.2. CURRENT RATING: 1.5 AMP;
- 3.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
- 3.4. WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
- 3.5. INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;

4. MECHANICAL:

- 4.1. MATING FORCE: 35N MAX.;
- 4.2. UNMATING FORCE: 5~35N;
- 4.3. OPERATING LIFE: 1500 CYCLES MIN.;

5. ENVIRONMENTAL:

- 5.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
- 5.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;
- 6.SALT SPRAY TEST:24H(EXCLUDING RIVETED BENDS)

C	外壳	SPCC	镀镍	
B	端子	黄铜+65	焊料区镀锡 接触区镀金(1U)	
A	基座	LCP	蓝色	
序号	品 名	材 质	电镀/ 颜色	备 注

东莞市文章济美电子有限公司

UNLESS OTHERWISE, GENERAL TOLERANCE:		NAME:		P/N:	
X.xxx ±0.10		3.0 A母贴板直脚平口		USB-3.0AF-BSSJ-B	
X.xx ±0.20		THIRD ANGLE PROJECTION		DWG NO.:	
X.x ±0.30		UNIT: mm		SCALE: 1:1	SIZE: A4
ANGULAR:		DRAWN:		SHEET: 1/1	REV.: A1
X.xx° ±1°		CHECKED:		APPROVED	
X.x° ±3°					
X° ±5°					