



REV.	ECN NO	LOCATIONS	DESCRIPTION	DATE







防水圈












Cap dimensions







PCB LAYOUT 图仅供参考

Note:
1.Material:
1.1 Housing:High temperature thermoplastic UL94v-0
1.2 Contact:Copper Alloy
1.3 InnerHousing:High temperature thermoplastic UL94v-0
1.4 OutShell: SUS
1.5 Middle plate:SUS
2.ELECTRICAL:
2-1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 3A Max
VBUS AND GND CONTACTS RATED AT 0.5A Min
0.9Amps Max.for all other contact.
PARALLELED FOR A TOTAL OF 5A;
2-2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2-3:DIEELECTRIC WITHSTANDING VOLTAGE:100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3-1:MATING FORCE:5~20N
3-2:UNMATING FORCE:8~20N(INITIAL),6~20N(AFTER 10000 CYCLES)
3-3:FREQUENCE:200±50 CYCLES/HOUR,10000 CYCLES
3-4:OPERATING TEMPERATURE;-40°~80°.
4:WATERPROOF:IP-X7.

TABLE B

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

PART NO:		MATERAL:	东莞市文章济美电子有限公司
MODEL NO:	XX	FINSH:	
UNIT: MM	SIZE: A4	COLOR:	TITLE: TYPE C 6PIN 直立式半包H6.8防水型母座 Z款
TOLERANCE UNSPECIFIED .x ±0.15 .xx ±0.10 .xxx ±0.05 Ang. ±1°		DR:	DWG NO: Type-C-6P-LTFSBBS-B REV: A
		CHK:	
		APP:	SCALE: 5:1 DATE: 2021.03.05