
















RECOMMENDED P.C.BOARD LAYOUT



NOTES:

1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
2.TERMINAL:PHOSPHOR BRONZE
3.CODING INFORMATION: BTB537-GxxS-COR

- PACKING: R: CARRIER REEL
- STANDARD TYPE
- COLOR:BEIGE
- RECEPTACLE
- PIN
- PLATING: G:GOLD FLASH
- 4:CONTACT AREA PLATING15u"Min GOLD.
- 0.8 BTB
- HEIGHT: 37--3.7H
- BTB CONNECTOR SERIES



3D VIEW

NO. of contacts	Dimensions					
	A	B	C	D	E	F
40	21.80	15.20	17.60	20.20	18.80	20.15
50	25.80	19.20	21.60	24.20	22.80	24.15
60	29.80	23.20	25.60	28.20	26.80	28.15
80	37.80	31.20	33.60	36.20	34.80	36.15
100	45.80	39.20	41.60	44.20	42.80	44.15
120	53.80	47.20	49.60	52.20	50.80	52.15
140	61.80	55.20	57.60	60.20	58.80	60.15
160	69.80	63.20	65.60	68.20	66.80	68.15
180	77.80	71.20	73.60	76.20	74.80	76.15
200	85.80	79.20	81.60	84.20	82.80	84.15

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD
CHECKED:	DATE:	TITLE: BTB0.8-80P AMP母座 塑高3.7 立贴带柱 (合高5.0)
DRAWN: YKX	DATE: 2026-6-26	PART.NO. Z-BTB0880P-F003
		UNIT mm SCALE free
		FILE NO. Ckmtw-BTB-C001 REV. A LXW0