




High photosynthesis 合高(H)	The female seat height 母座单高(H1)	The male seat height 公座单高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9

Part No	CKT	A	B	C	D	E
BTB0.8-MH3.0-8PALTI	8	2.40	3.50	5.10	4.20	4.00
BTB0.8-MH3.0-10PALTI	10	3.20	4.30	5.90	5.00	
BTB0.8-MH3.0-12PALTI	12	4.00	5.10	6.70	5.80	
BTB0.8-MH3.0-14PALTI	14	4.80	5.90	7.50	6.60	
BTB0.8-MH3.0-16PALTI	16	5.60	6.70	8.30	7.40	
BTB0.8-MH3.0-18PALTI	18	6.40	7.50	9.10	8.20	
BTB0.8-MH3.0-20PALTI	20	7.20	8.30	9.90	9.00	
BTB0.8-MH3.0-22PALTI	22	8.00	9.10	10.70	9.80	
BTB0.8-MH3.0-24PALTI	24	8.80	9.90	11.50	10.60	8.00
BTB0.8-MH3.0-26PALTI	26	9.60	10.70	12.30	11.40	
BTB0.8-MH3.0-28PALTI	28	10.40	11.50	13.10	12.20	
BTB0.8-MH3.0-30PALTI	30	11.20	12.30	13.90	13.00	
BTB0.8-MH3.0-32PALTI	32	12.00	13.10	14.70	13.80	
BTB0.8-MH3.0-34PALTI	34	12.80	13.90	15.50	14.60	
BTB0.8-MH3.0-36PALTI	36	13.6	14.70	16.30	15.40	
BTB0.8-MH3.0-38PALTI	38	14.40	15.50	17.10	16.20	
BTB0.8-MH3.0-40PALTI	40	15.20	16.30	17.90	17.00	41.00
BTB0.8-MH3.0-44PALTI	44	16.80	17.90	19.50	18.60	
BTB0.8-MH3.0-50PALTI	50	19.20	20.30	21.90	21.00	
BTB0.8-MH3.0-60PALTI	60	23.20	24.30	25.90	25.00	
BTB0.8-MH3.0-70PALTI	70	27.20	28.30	29.90	29.00	
BTB0.8-MH3.0-80PALTI	80	31.20	32.30	33.90	33.00	
BTB0.8-MH3.0-100PALTI	100	39.20	40.30	41.90	41.00	

技术指标:

- 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
- 3. 额定电压: 125V, AC。
- 4. 接触电阻: $\leq 0.02\ \Omega$ 。
- 5. 绝缘电阻: $\geq 100\text{M}\ \Omega$ 。

序号	品名	材质
①	0.8 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0, 颜色: 黑色
②	0.8 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0, 颜色: 黑色

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.50	$\pm 1^{\circ}$	PART NO. BTB0.8-MH3.0-NPALT1	TITLE: 0.8 Pitch双槽立式BTB母座业务图(单高3.0)	
.X ± 0.20		DESIGN: James	CUSTOMER	SIZE A4
.XX ± 0.10		CHED: Talen		UNITS MM
MANUFACTURE DWG		APPD: Sophia		SCALE N:A
				SHEET 1/1