









RECOMMENDED P.C.B HOLE LAYOUT
TOP VIEW(TOLERANCE:±0.05)

5	SHELL-B	SUS201	T=0.25	Ni:40u"Min	1
4	SHELL-A	SPCC	T=0.30	Ni:40u"Min	4
3	TERMINAL-A	BRASS	T=0.2	Sn60u"+Au G/F	18
2	Subject	PBT	/	Blue	1
1	HOUSING	PBT	/	Blue	1
NO.	Part Name	MATERIAL	THICK	FINISH	Q' TY

REV	DESCRIPTION	DATE	APPROVED
A	初版发行	2023.09.18	Peter Tan

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminc
- 2.额定电压: Voltage Rating
30V DC
- 3.接触电阻: Contact Resistance
30 milliohms MAX
- 4.耐电压: Dielectnc Withstanding Voltage
300 V AC AT Sea Lve
- 5.绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force
Mate force:1.0 kgf(MAX)
Unmate force:0.7kgf(MIN)
- 2.端子保持力: Terminal Retenion
0.3 kgf(MIN)

原材料:Material:

- 1.塑胶:Housing:
Hing Temperature Tneaplastic
UIPBT Blue /Black
- 2.端子:Contact:Copper Alloy
- 3.外壳:Shell: Copper Alloy SPCC/C268

电镀:Finish:

- 1.端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
- 2.外壳:Shell:
Nickel Plating

CUSTOMER DRAWING			东莞市文章济美电子有限公司		
UNITS mm	SCALE 1:1	SHEET 1 OF 1	TITLE USB AF 双层3.0 90度 短体卷边 带后盖弹片连体 PBT蓝色1u插板		
PROJECTION: 	DRAW:		MAT'L SEE TABLE		
GENERAL TOLERANCE 0. ±0.35 0.0 ±0.25 0.00 ±0.15 0.° ±4° 0.0° ±3°	CHECK:		FINISH SEE TABLE		
	APPD:		DWG. NO. USB-3.0AFSC90DU-B		
			PART NO.	SIZE A4	