

电气特性:Electrical:

3A/contact terminal

30V DC

30 milliohms MAX

500 V AC AT Sea Level

1000MEGA ohms MIN

Mate force:3.57kgf(MAX)

1. 塑胶:Housing:

2.端子:Contact:Copper Alloy C2680





3.外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish: Tin On Solder Talls

端子四周镀60U”(MIN)—100U锡, ”镀金1U”

蠟壳四周鍍80U”(MIN)鍍

Nickel Plating



PIN NU_BER	SIGNAL NAME
1	USB 电压 VBUS
2	D-(负极)
3	D+(正极)
4	地线
5	SSRX-
6	SSRX+
7	GND(地线)
8	SSTX-
9	SSTX+
shell	SHIELD

成 品 圖 MANUFACTURE DWG		东莞市文章济美电子有限公司									
公差一覽表 TOLERANCE UNLESS OTHERWISE											
.X±0.20	.X±5*	日期 DATE	2023.04.27	單位 UNIT	MM	制圖 DRAWING		DWG NO.	USB-3.0AF-DT10.0BS6.3H-B		
XX±0.10	.X±2*	审核 CHECKED		比例 SCALE	1 : 1	设计 DESIGN	LIUFU	品名 NAME			
XXX±0.02	.XX±1*	核准 APPROVE		角法 VIEW				版本 VER.	AO	页 SHEET	001