










RECOMMENDED P.C.B LAYOUT



1	VBUS
2	D-
3	D+
4	GND
5	StdB_SSRX-
6	StdB_SSRX+
7	GND_DRAIN
8	StdB_SSTX-
9	StdB_SSTX+
PIN	SIGNAL NAME

规格型号:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触阻抗: Contact Resistance
30 milliohms MAX
- 4.耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.阻抗: Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion
1.0kgf(MIN)

原材料:Material:

- 1.塑膠:Housing:
Hing Temperature Tnermaplastics,
LCP Blue
- 2.端子:Contact:Copper Alloy C2680/C5191
- 3.外壳:Shell: SPCC/C2680

电镀:Plating:

- 1.端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
端子四周镀80U"(MIN)锡; 50U"(MIN)Ni; 1U" Au
- 2.外壳:Shell:
外壳四周镀60U"(MIN) Ni&Cu

3	Housing	LCP Blue			
2	Contact	C2680			
1	Shell	SPCC /C2680			
ITEM	DESC.	MATERIAL	REMARKS	PART	REMARKS
APPROVED	CHECKED	DESIGN	DRAWN	PART NO.	USB-3.0AM-CBDZ90DU-B SHT 1/1
				DESCRIPTION	USB 3.0 AM 沉板弯脚 DIP H1.9 有柱 (工程?)
				DRAWING NO.	REV A/0

QUALITY SYMBOLS	UNIT	SCALE	TOLERANCES
□ : CRITICAL ■ : MAJOR ▽ : ZERO DEFECT ▽ : S.P.C	mm	1:1	X±0.20 XX±0.10 XXX±0.05 X±5° X±3° XX±2°
东莞市文章济美电子有限公司			
DIP	2023-06-01		
A/0	2021-12-01		
REV	DESCRIPTION/ECN.NO	DATE	