






PRODUCT SPECIFICATION

版本号  
Version Number: 2020/05

产品编码  
PART Number: FW20002AWR



A-A

技术参数 SPECIFICATIONS

温度范围 (Temperature range): -25° C~+85° C  
额定电压 (Voltage rating): 250V.Ac/Dc  
额定电流 (Current rating): 2A  
接触电阻 (Contact resistance): ≤20M Ω  
绝缘电阻 (Insulation resistance): ≥1000M Ω  
耐压 (Withstand voltage): 1000V.Ac/1min  
材料 (Material):  
针座 (Wafer): LCP UL94V-0  
插针 (Terminal): 黄铜 (Rhoso.bronze Tin/plated)  
贴片 (Wafer): 黄铜 (Rhoso.bronze Tin/plated)

包装方式 (Package): 贴片 (Wafer)

散装 Loosen Package  
管装 Pipe Package  
编带 Tape Reel Package

浙江博穆精密电子有限公司

|                       |  |                                      |  |                               |  |
|-----------------------|--|--------------------------------------|--|-------------------------------|--|
| 设计: 林加才               |  | 名称 TITLE:<br>2.00 Pitch HY Connector |  | DRAW NAME:<br>HY2.0-A 贴片卧式连接器 |  |
| 审核: 金加成               |  | SERIES:                              |  | DRAW NO.                      |  |
| 批准: 朱青峰               |  | P/N:                                 |  | UNIT: mm                      |  |
| CUSTOMER DRAWING 客户图纸 |  | REV. 1.00 SCALE N/A                  |  | SHEET: 1/1                    |  |

|      |       |       |       |      |       |       |       |
|------|-------|-------|-------|------|-------|-------|-------|
| 8    | 20.00 | 14.00 | 18.50 | ...  | ...   | ...   | ...   |
| 7    | 18.00 | 12.00 | 16.50 | 14   | 32.00 | 26.00 | 30.50 |
| 6    | 16.00 | 10.00 | 14.50 | 13   | 30.00 | 24.00 | 28.50 |
| 5    | 14.00 | 8.00  | 12.50 | 12   | 28.00 | 22.00 | 26.50 |
| 4    | 12.00 | 6.00  | 10.50 | 11   | 26.00 | 20.00 | 24.50 |
| 3    | 10.00 | 4.00  | 8.50  | 10   | 24.00 | 18.00 | 22.50 |
| 2    | 8.00  | 2.00  | 6.50  | 9    | 22.00 | 16.00 | 20.50 |
| POS. | DIM.A | DIM.B | DIM.C | POS. | DIM.A | DIM.B | DIM.C |