









技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 适用线规: AWG#28~#22。
4. 额定电压: 250V DC/AC(rms)。
5. 额定电流: 3.0A AC, DC。
6. 接触电阻: $\leq 20\text{m}\Omega$ 。
7. 耐压值: 800V AC/minute。
8. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。



3	2.0A型双排立式WTB吸盖	LCP UL94V-0 本色
2	2.0A型立式(连续)端子	铜合金/表面镀锡
1	2.0A型双排立式WTB胶芯	LCP UL94V-0 本色
序号	名称	材质

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

型号	CKT	A	B	C
D-PHB2.0-L2-M2P42	2*2	2.00	6.00	3.00
D-PHB2.0-L2-M3P42	2*3	4.00	8.00	3.00
D-PHB2.0-L2-M4P42	2*4	6.00	10.00	3.00
D-PHB2.0-L2-M5P42	2*5	8.00	12.00	5.00
D-PHB2.0-L2-M6P42	2*6	10.00	14.00	7.00
D-PHB2.0-L2-M7P42	2*7	12.00	16.00	9.00
D-PHB2.0-L2-M8P42	2*8	14.00	18.00	11.00
D-PHB2.0-L2-M9P42	2*9	16.00	20.00	13.00
D-PHB2.0-L2-M10P42	2*10	18.00	22.00	15.00
D-PHB2.0-L2-M11P42	2*11	20.00	24.00	17.00
D-PHB2.0-L2-M12P42	2*12	22.00	26.00	19.00
D-PHB2.0-L2-M13P42	2*13	24.00	28.00	21.00
D-PHB2.0-L2-M14P42	2*14	26.00	3.00	23.00
D-PHB2.0-L2-M15P42	2*15	28.00	32.00	25.00
D-PHB2.0-L2-M16P42	2*16	30.00	34.00	27.00
D-PHB2.0-L2-M18P42	2*18	34.00	38.00	31.00
D-PHB2.0-L2-M20P42	2*20	38.00	42.00	35.00
D-PHB2.0-L2-M22P42	2*22	42.00	46.00	39.00



PCB.WELDING DRAWING (TOLERANCE:±0.05)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO.	TITLE:		
.XX±0.25	X.X°±1°	D-PHB2.0-L2-MNP42	2.0 Pitch A型双排立贴WTE		
.XXX±0.15		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				